

# Locking Devices, Twist-Lock®, Watertight Safety Shroud®, Receptacle, 20A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-20R, Screw Terminal, Gray



By Hubbell Wiring Device-Kellems  
Catalog # [HBL2510SW](#)

Locking Devices, Twist-Lock®, Watertight Safety-Shroud®, Receptacle, 20A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, NEMA L21-20R, Screw Terminal, PBT housing and flange, Gray.

## Application

Heavy Duty Industrial Shrouded Watertight

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL2510SW
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Horsepower - Maximum	2
Item Type	20A Watertight Safety-Shroud® Receptacle
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> <li>• Body Contact Carrier - Natural (white) nylon</li> <li>• Contacts - Brass</li> <li>• Drive Screws - Steel, zinc plated</li> <li>• Housing / Cover - Gray RPT</li> </ul>

Type  
UPC

- Lift-Cover Spring & Pin - Stainless Steel
  - Terminal Retainer - Clear polycarbonate
- Receptacle  
783585231501

## Dimensions

Dimensions	3.75 in x 3.75 in x 2.9 in
Display Size	Standard Sized Product
Height	2.9 in
Length	3.75 in
Weight	0.65 lb
Width	3.75 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	3 Phase WYE
Voltage Rating	3 Phase WYE 120/208 VAC
Voltage Rating Description	3-Phase Y 120/208 VAC

## Conductor Related

Number Of Wires	5-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L21-20R

## Logistics

Carton Quantity 5  
Pallet Quantity 950

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL2510SW](#)  
[Warranty - Industrial & Commercial Products](#)

## Product Assets

---



©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL2510SW-SPEC-EN | REV 10/2024