

Locking Devices, Twist-Lock®, Industrial, Male Plug, 20A 3-Phase 120/208VAC, 4-Pole 5-Wire Grounding, L21-20P, Screw Terminal, Black and White



By Hubbell Wiring Device-Kellems
Catalog # [HBL2511](#)

Locking Devices, Twist-Lock®, Industrial, Male Insulgrip® Plug, 20A 3-Phase WYE 120/208VAC, 4-Pole 5-Wire Grounding, NEMA L21-20P, Screw Terminal, Black and White Nylon.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2511
Color	Noir, blanc
Cord Range	0.350"-1.150" (9-29)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	20A Male Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Steel - nickel plated• Blades - Brass• Housing / Cord Clamp - Nylon• Terminal Clamp - Cold rolled steel - nickel plated• Terminal Retainer - Clear polycarbonate

Type
UPC

- Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- Plugs
783585038537

Dimensions

Dimensions	2.33 in x 2.33 in x 2.75 in
Display Size	Standard Sized
Height	2.75 in
Length	2.33 in
Weight	0.3 lb
Width	2.33 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	3 Phase WYE
Voltage Rating	3 Phase WYE 120/208 VAC
Voltage Rating Description	3 Phase WYE 120/208 VAC

Conductor Related

Cable Range	0.350 - 1.150 in
Cord Type	All Listed Portables
Number Of Wires	5-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L21-20P

Logistics

Carton Quantity	30
Pallet Quantity	3060

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL2511](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2511-SPEC-EN | REV 10/2024