

## Locking Devices, Hubbellock, Industrial, Receptacle, 30A 600V AC, 20A 250V DC, 4-Pole 5-Wire Grounding, Non NEMA, Screw Terminal, With FS/FD Cover.

By Hubbell Wiring Device-Kellems  
Catalog # [HBL25250](#)



Hubbellock® Industrial Receptacle, 30A 600V AC, 20A 250V DC, 4-Pole 5-Wire Grounding phenolic interior weatherproof housing, Non NEMA, Screw Terminal, with FS/FD Cover

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 2,000V minimum
- Environmental - Flammability - UL 94 V0 for Receptacles and Inlets.HB or better for Plugs and Connectors
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accomodation - #10 AWG - #6 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL25250
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A/30A Grounding Hubbellock® Receptacle
Material	Aluminum, Cast
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Contacts - Brass</li><li>• Housing - Cast aluminum</li><li>• Receptacle Interior - Thermoset</li><li>• Terminal Screws - Zinc plated steel</li></ul>
Type	Receptacle
UPC	783585017594

### Dimensions

Dimensions	4.56 in x 3.28 in x 3.67 in
Display Size	Standard Sized Product
Height	3.67 in
Length	4.56 in
Weight	1.3 lb
Width	3.28 in

### Electrical Ratings

Amperage Rating	20/30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20/30 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

### Conductor Related

Number Of Wires	5-Wire
Wire Size	#10 AWG to #6 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA Standard</li><li>• Listed to UL Standard</li></ul>
----------------------	---

### Logistics

Carton Quantity	5
Pallet Quantity	770

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL25250](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand