



Locking Devices, Hubbellock, Industrial, Receptacle, 30A 600V AC, 20A 250V DC, 4-Pole 5-Wire Grounding, Non NEMA, Screw Terminal, Blue.

By Hubbell Wiring Device-Kellems
Catalog # [HBL25403](#)



Locking Devices, Hubbellock®, Industrial, Receptacle, 30A 600V AC, 20A 250V DC, 4-Pole 5-Wire Grounding, Black phenolic interior, Aluminum housing, Non NEMA, Screw Terminal, Blue

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Metallic housing provides protection from damage in harsh environments

Application

Heavy Duty Industrial

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A/30A Grounding Hubbellock® Receptacle
Material	Aluminum, Cast
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - 2,000V minimum • Environmental - Flammability - UL 94 V0 for Receptacles and Inlets.HB or better for Plugs and Connectors • Environmental - Moisture Resistance - IP30 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C. Minimum

Dimensions

Dimensions	4.56 in x 2.84 in x 2.94 in
Display Size	Standard Sized Product
Height	2.94 in
Length	4.56 in
Weight	0.95 lb
Width	2.84 in

Electrical Ratings

Amperage Rating	20/30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20/30 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Number Of Wires	5-Wire
Wire Size	#10 AWG to #6 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA Standard • Listed to UL Standard
----------------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Continuous 75 °C, Minimum
-40°C (w/o impact)

- Mechanical - Terminal Accomodation - #10 AWG - #6 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Type

- Receptacle
- Receptacle

UPC

783585017464



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL25403-SPEC-EN | REV 1/2024