

# Watertight Devices, Twist-Lock® Connector, 15A, 250V AC, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA L6-15R, Yellow



By Hubbell Wiring Device-Kellems  
Catalog # [HBL25W49](#)

Watertight Devices, Twist-Lock® Connector, 15A, 250V AC, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA L6-15R, Yellow

## Performance

- Electrical - Current Interrupting - Rated for current interruption per UL498
- Electrical - Dielectric Voltage - 2500V AC
- Electrical - Max Working Voltage - As marked
- Electrical - Temperature Rise - 30°C max per UL498 at rated current
- Environmental - UV resistance - All exposed materials are UV stabilized
- Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P
- Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous
- Mechanical - Cord Accommodation - 0.375"-0.625" (9.5-15.9)

## General

Catalog Number	HBL25W49
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Item Type	15A Watertight Twist-Lock® Connector
Number Of Poles	2-Pole
Type	Connector Body
UPC	783585131337

## Dimensions

Dimensions	1.85 in x 1.85 in x 4.62 in
Height	4.62 in

Length	1.85 in
Width	1.85 in

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	16/3 SJ to 10/3 SJ, 18/3 S to 12/3 S

## Certifications And Compliance

Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	L6-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	25
-----------------	----

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBL25W49](#)
- [Warranty - Industrial & Commercial Products](#)