

HUBBELL
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,
Safety Shroud, 2-Gang Semi Flush
Receptacle, 30A 125V, 2-Pole 3-
Wire Grounding, L5-30R, Screw
Terminal, Gray**

By Hubbell Wiring Device-Kellems
Catalog # [HBL2610SR2](#)

Locking Devices, Twist-Lock®, Safety-Shroud®, 2-Gang Semi
Flush Receptacle, 30A 125V AC, 2-Pole 3-Wire Grounding, NEMA
L5-30R, Screw Terminal, Gray



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2610SR2
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	30A Safety-Shroud® Receptacle
Material	Valox™
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Number of Gang(s)	2-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Body Contact Carrier - Natural (white) nylon• Body Holding Screws - Steel, zinc plated• Contacts - Brass• Housing / Flange - Gray RPT• Terminal Retainer - Clear polycarbonate
Type	Semi Flush Receptacle
UPC	783585234281

Dimensions

Dimensions	5.12 in x 5.12 in x 2.22 in
Display Size	Standard Sized Product
Height	2.22 in
Length	5.12 in
Weight	0.6 lb
Width	5.12 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L5-30R

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL2610SR2](#)
[Warranty - Industrial & Commercial Products](#)

