



# Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2611](#)



Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White.

## Features

- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.

## Application

Extra Heavy Duty Industrial

## General

|                              |  |
|------------------------------|--|
| Color                        | Noir, blanc  |
| Cord Range                   | 0.360"-0.930" (9-24)                                     |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means          |
| Horsepower - Maximum         | 2  |
| Item Type                    | 30A Grounding Insulgrip® Plug                            |
| Material                     | Nylon  |
| Material - Mounting Hardware | Cord Mounted   |
| Number Of Poles              | 2-Pole   |
| Operating Temperature        | Maximum continuous 75°C and minimum -40°C without Impact |

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 2.26 in x 2.26 in x 2.75 in |
| Display Size | Standard Sized              |
| Height       | 2.75 in                     |
| Length       | 2.26 in                     |
| Weight       | 0.25 lb                     |
| Width        | 2.26 in                     |

## Electrical Ratings

|                            |                           |
|----------------------------|---------------------------|
| Amperage Rating            | 30 A                      |
| Connectivity               | Pressure Terminal Screws  |
| Current / Amperage Rating  | 30 A                      |
| Current Rating             | 30 A                      |
| Dielectric Strength        | Withstands 2,000V minimum |
| Phase                      | Single Phase              |
| Voltage Rating             | 125 VAC                   |
| Voltage Rating Description | 125 VAC                   |

## Conductor Related

|                 |                      |
|-----------------|----------------------|
| Cable Range     | 0.360 - 0.930 in     |
| Cord Type       | All Listed Portables |
| Number Of Wires | 3-Wire               |
| Wire Size       | #16 AWG to #8 AWG    |

## Certifications and Compliance

|                      |   |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul> |
|----------------------|---|

|                                    |        |
|------------------------------------|--------|
| Nema Rating                        | L5-30P |
| Standards - RoHS Compliance Status | CM     |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 30 |
|-----------------|----|

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

Copper wire only.

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Type

- Plugs
- Plugs

UPC

783585038735



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL2611-SPEC-EN | REV 1/2024