



# Locking Devices, Twist-Lock®, Safety Shroud, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2611S](#)



Locking Devices, Twist-Lock®, Safety-Shroud®, Male Plug, 30A 125V AC, 2-Pole 3-Wire Grounding, NEMA L5-30P, Screw Terminal, Black and White Nylon Body, White PBT Shroud.

## Features

- Ribbed nylon housing provides a secure grip and impact and chemical resistance
- Superior cord grip design protects terminations from excess strain
- Integral dust shield protects wiring chamber from dust or contaminants

## Application

Extra Heavy Duty Industrial

## General

Color	Black, White
Cord Range	0.360"-0.930" (9-24)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	30A Safety-Shroud® Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal</li> </ul>

## Dimensions

Dimensions	2.26 in x 2.26 in x 4.21 in
Display Size	Standard Sized
Height	4.21 in
Length	2.26 in
Weight	0.35 lb
Width	2.26 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Cable Range	0.360 - 0.930 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	L5-30P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Wiring B-28 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

Accommodation - #16  
AWG - #8 AWG stranded  
copper wire only.

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Type

- Plugs
- Plugs

UPC

783585234304



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL2611S-SPEC-EN | REV 1/2024