



# Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 125V 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2615](#)



Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 125V 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, White

## Features

- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

## Application

Extra Heavy Duty Industrial

## General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Grounding Insulgrip® Flanged Inlet
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C. Minimum -40°C (w/o impact)</li> <li>• Mechanical - Cord Grip Accomodation - #16 AWG - #8 AWG solid or stranded copper wire only.</li> <li>• Mechanical - Terminal Identification - Terminals</li> </ul>

## Dimensions

Dimensions	2.88 in x 2.88 in x 2.09 in
Display Size	Standard Sized Product
Height	2.09 in
Length	2.88 in
Weight	0.20 lb
Width	2.88 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
----------------------	---

Nema Rating	L5-30P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

identification - terminals  
identified in accordance  
with UL 498

Type

- Flanged Inlet
- Flanged Inlet

UPC

783585038797



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL2615-SPEC-EN | REV 1/2024