



Locking Devices, Twist-Lock®, Safety-Shroud® Receptacle, 30A, 250V AC, 2 Pole, 3 Wire Grounding, NEMA L6-30R, RPT surface mounting, One Gang, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBL2620SR](#)



Locking Devices, Twist-Lock®, Safety-Shroud® Receptacle, 30A, 250V AC, 2 Pole, 3 Wire Grounding, NEMA L6-30R, RPT surface mounting, One Gang, Gray

Application

Heavy Duty Industrial Shrouded

General

Color	<ul style="list-style-type: none"> • Gray, White • Gris, Blanc
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	30A Safety-Shroud® Receptacle
Listings	<ul style="list-style-type: none"> • UL 498 • Fed.Spec. W-C-596 • CSA C22.2 No.42
Material	Valox™
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical-Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only • Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 • Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture Resistance - IP20

Dimensions

Dimensions	4.56 in x 2.84 in x 1.58 in
Display Size	Standard Sized Product
Height	1.58 in
Length	4.56 in
Weight	0.45 lb
Width	2.84 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 VAC

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#16 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
----------------------	---

Nema Rating	L6-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Wiring H-15 Catalog page](#)
[Catalog Page - Wiring C-12 Catalog page](#)
[Catalog Page - Wiring B-29 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Suitability

- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)

UPC

783585234342



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL2620SR-SPEC-EN | REV 1/2024