



# Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 250V, 2-Pole 3-Wire Grounding, L6-30P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2621](#)



Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 250V, 2-Pole 3-Wire Grounding, L6-30P, Screw Terminal, Black and White.

## Features

- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.

## Application

Extra Heavy Duty Industrial

## General

Color	Noir, blanc
Cord Range	0.360"-0.930" (9-24)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	30A Grounding Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only

## Dimensions

Dimensions	2.26 in x 2.26 in x 2.75 in
Display Size	Standard Sized
Height	2.75 in
Length	2.26 in
Weight	0.25 lb
Width	2.26 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

## Conductor Related

Cable Range	0.360 - 0.930 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
----------------------	---

Nema Rating	L6-30P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	30
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

Copper wire only.

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Type

- Plugs
- Plugs

UPC

783585038834



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL2621-SPEC-EN | REV 1/2024