



Locking Devices, Twist-Lock®, Watertight Safety-Shroud® Connector, 30A, 250V AC, 2 Pole, 3 Wire Grounding, NEMA L6-30R PBT housing PBT clamps.



By Hubbell Wiring Device-Kellems
Catalog # [HBL2623SW](#)

Locking Devices, Twist-Lock®, Watertight Safety-Shroud®
Connector, 30A, 250V AC, 2 Pole, 3 Wire Grounding, NEMA
L6-30R, Black PBT housing, White PBT clamps.

Application

Heavy Duty Industrial

General

Color	Black, White
Cord Range	0.360"-0.930" (9-24)
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	30A Watertight Safety-Shroud® Connector
Listings	<ul style="list-style-type: none"> • UL 498 • Fed.Spec. W-C-596 • CSA C22.2 No.42 • UL Listed • CSA Certified to Type 4, 4X and Type 12
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical-Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only • Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 • Environmental - Flammability - V0 per UL94/CSA 22.2 No.0.17 • Environmental - Moisture

Dimensions

Dimensions	4.4 in x 2.57 in x 2.57 in
Display Size	Standard
Height	2.57 in
Length	4.4 in
Weight	0.55 lb
Width	2.57 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L6-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Wiring C-3 Catalog page](#)
[Catalog Page - Wiring B-29 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Resistance - Type 4, 4X, 12,
IP66 suitability

- Environmental - Operating
Temperatures - Maximum
Continuous 75°C

- Minimum -40°C (w/o
impact)

Type

- Connector

- Connector

UPC

783585231709



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL2623SW-SPEC-EN | REV 1/2024