

Locking Devices, Hubbellock, Industrial, Female Connector Body, 60A 600V AC, 3-Pole 4-Wire Grounding, Non NEMA, Screw Terminal, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL26418](#)



Locking Devices, Hubbellock®, Industrial, Female Connector Body, 60A 600V, 3-Pole 4-Wire Grounding, Black phenolic interior, Non NEMA, Screw Terminal, Yellow thermoplastic sleeve over steel housing

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage Withstand - 2,000V minimum
- Environmental - Flammability - UL 94 VO
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #8 AWG - #4 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL26418
Color	Yellow
Cord Range	0.920"-1.450" (23.36-36.83)
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	60A Grounding Hubbellock® Connector
Material	Steel
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Connector Interior - Phenolic • Contacts / Springs - Copper alloy • Cord Clamp - Steel • Device Color - Yellow • Housing - Steel Housing / Yellow Polycarbonate Cover • Terminal - Copper

Type
UPC

• Terminal Screws - Stainless steel
Connector Body
783585017310

Dimensions

Dimensions	3.19 in x 1.09 in x 5.44 in
Display Size	Standard
Height	5.44 in
Length	3.19 in
Weight	2.45 lb
Width	1.09 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	600 V
Voltage Rating Description	600 V

Conductor Related

Cable Range	0.920 - 1.450 in
Number Of Wires	4-Wire
Wire Size	#8 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No. 42 • Listed to UL 498
----------------------	---

Logistics

Carton Quantity	5
Pallet Quantity	770



A Hubbell brand