

Locking Devices, Hubbellock, Industrial, Flanged Receptacle, 60A 600V AC, 3-Pole 4-Wire Grounding, Non NEMA, Screw Terminal, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL26421](#)

Hubbellock® Industrial Flanged Receptacle, 60A 600V, 3-Pole
4-Wire Grounding phenolic interior with Steel housing and
flange, Non NEMA, Screw Terminal



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 2,000V minimum
- Environmental - Flammability - UL 94 V0
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accomodation - #8 AWG - #4 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL26421
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	60A Grounding Hubbellock® Flanged Receptacle
Material	Steel, Zinc Plated
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Contacts / Springs - Copper alloy• Flanged Housing - Zinc plated steel• Receptacle Interior - Phenolic• Terminal - Copper• Terminal Screws - Stainless steel
Type	Flanged Receptacle
UPC	783585017600

Dimensions

Dimensions	4.12 in x 2.88 in x 4.53 in
Display Size	Standard Sized Product
Height	4.53 in
Length	4.12 in
Weight	2.05 lb
Width	2.88 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Screw Terminals
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Multi Phase
Voltage Rating	600 V
Voltage Rating Description	600 V

Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA Standard• Listed to UL Standard
----------------------	---

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL26421](#)
[Warranty - Industrial & Commercial Products](#)