

Locking Devices, Hubbellock, Industrial, Female Connector Body, 60A 600V AC, 4-Pole 5-Wire Grounding, Non NEMA, Screw Terminal, Blue



By Hubbell Wiring Device-Kellems
Catalog # [HBL26516](#)

Hubbellock® Industrial Female Connector Body, 60A 600V AC,
4-Pole 5-Wire Grounding phenolic interior, Non NEMA, Screw
Terminal thermoplastic sleeve over Steel cover

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage Withstand - 2,000V minimum
- Environmental - Flammability - UL 94 VO
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #8 AWG - #4 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL26516
Color	Blue
Cord Range	1.00"-1.50"(25.40-38.10)
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	60A Grounding Hubbellock® Connector
Material	Steel
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Connector Interior - Phenolic• Contacts / Springs - Copper alloy• Cord Clamp - Steel• Device Color - Blue• Housing - Steel Housing / Blue Polycarbonate Cover• Terminal - Copper

Type
UPC

- Terminal Screws - Stainless steel
- Connector Body
783585017501

Dimensions

Dimensions	3.19 in x 1.09 in x 5.44 in
Display Size	Standard
Height	5.44 in
Length	3.19 in
Weight	2.5 lb
Width	1.09 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	600 VAC
Voltage Rating Description	600 VAC

Conductor Related

Cable Range	1.000 - 1.50 in
Number Of Wires	5-Wire
Wire Size	#8 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Listed to UL 498
----------------------	---

Logistics

Carton Quantity	5
-----------------	---

Product Assets



A Hubbell brand