

# Locking Devices, Twist-Lock®, Marine Grade, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Yellow



By Hubbell Wiring Device-Kellems  
Catalog # [HBL26CM13](#)

Locking Devices, Twist-Lock®, Marine Grade, Female Insulgrip® Connector Body, 30A 125V AC, 2-Pole 3-Wire Grounding, NEMA L5-30R, Screw Terminal, Yellow Nylon.

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL26CM13
Color	Yellow
Cord Range	0.360"-0.930" (9-24)
EU RoHS Indicator	Yes
Environmental Conditions	Corrosion Resistant
Insulation	Insulated Body
Item Type	30A Corrosion Resistant Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Steel - nickel plated</li><li>• Contacts - Nickel Plated Brass</li><li>• Housing / Cord Clamp - Nylon</li><li>• Terminal Clamp - Cold rolled steel - nickel plated</li><li>• Terminal Retainer - Clear polycarbonate</li></ul>

Type  
UPC

- Terminal Screws - #10-32 Bronze (Phillips / Slotted / Robertson)
- Connector Body  
783585039091

## Dimensions

Dimensions	2.26 in x 2.26 in x 3.86 in
Display Size	Standard
Height	3.86 in
Length	2.26 in
Weight	0.4 lb
Width	2.26 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

## Conductor Related

Cable Range	0.360 - 0.930 in
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Fed.Spec. W-C-596</li><li>• Listed to UL 498</li></ul>
Nema Rating	L5-30R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	720

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL26CM13](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL26CM13-SPEC-EN | REV 1/2025