

## Watertight Devices, Twist-Lock® Plug, 20A, 3 Phase WYE 120/208V AC, 4 Pole, 4 Wire, Thermoplastic elastomer, NON-NEMA, Yellow

By Hubbell Wiring Device-Kellems  
Catalog # [HBL26W09](#)



Watertight Twist-Lock® Plug, 20A, 3 Phase WYE 120/208V AC, 4-Pole, 4 Wire, Thermoplastic elastomer, NON-NEMA

### Performance

- Electrical - Current Interrupting - Rated for current interruption per UL498
- Electrical - Dielectric Voltage - 2500V AC
- Electrical - Max Working Voltage - As marked
- Electrical - Temperature Rise - 30°C max per UL498 at rated current
- Environmental - UV resistance - All exposed materials are UV stabilized
- Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P
- Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous
- Mechanical - Cord Accommodation - 0.375"-0.875" (9.5-22.2)

### General

Catalog Number	HBL26W09
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Item Type	20A Watertight Twist-Lock® Plug
Number Of Poles	4-Pole
Type	Plugs
UPC	783585456300

### Dimensions

Dimensions	2.77 in x 2.77 in x 3.94 in
Height	3.94 in

Length	2.77 in
Width	2.77 in

### Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	3-Phase Y 120/208 VAC
Voltage Rating Description	3-Phase Y 120/208 VAC

### Conductor Related

Number Of Wires	4-Wire
Wire Size	Min Cords: 12/3 SJ, 16/3 S, 14/4 SJ, 18/4 S, 18/5 S;Max Cord: 8/3 S, 8/4 S, 10/5 S

### Certifications And Compliance

Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	Non-NEMA

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBL26W09](#)
- [Warranty - Industrial & Commercial Products](#)