

## Watertight Devices, Twist-Lock® Plug, 20A, 277V AC, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA L7-20P, Yellow

By Hubbell Wiring Device-Kellems  
Catalog # [HBL26W49](#)



Watertight Devices, Twist-Lock® Plug, 20A, 277V AC, 2 Pole, 3 Wire, Thermoplastic elastomer, NEMA L7-20P, Yellow

### Performance

- Electrical - Current Interrupting - Rated for current interruption per UL498
- Electrical - Dielectric Voltage - 2500V AC
- Electrical - Max Working Voltage - As marked
- Electrical - Temperature Rise - 30°C max per UL498 at rated current
- Environmental - UV resistance - All exposed materials are UV stabilized
- Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P
- Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous
- Mechanical - Cord Accommodation - 0.375"-0.875" (9.5-22.2)

### General

Catalog Number	HBL26W49
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Item Type	20A Watertight Twist-Lock® Plug
Number Of Poles	2-Pole
Type	Plugs
UPC	783585131412

### Dimensions

Dimensions	2.51 in x 2.51 in x 3.96 in
Height	3.96 in
Length	2.51 in

Width 2.51 in

### Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	277 VAC
Voltage Rating Description	277 VAC

### Conductor Related

Number Of Wires	3-Wire
Wire Size	Min. Cord: 16/3 SJ, 18/3 S, 18/4 SJ, 18/4 S, 18/5 S;Max. Cord: 10/3 S, 10/4 S, 10/5 S

### Certifications And Compliance

Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	L7-20P
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
Pallet Quantity	850

### Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBL26W49](#)
- [Warranty - Industrial & Commercial Products](#)