

Watertight Devices, Twist-Lock® Plug, 20A, 3 Phase 480V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L16-20P, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL26W76](#)



Watertight Devices, Twist-Lock® Plug, 20A, 3 Phase 480V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L16-20P, Yellow

Performance

- Electrical - Current Interrupting - Rated for current interruption per UL498
- Electrical - Dielectric Voltage - 2500V AC
- Electrical - Max Working Voltage - As marked
- Electrical - Temperature Rise - 30°C max per UL498 at rated current
- Environmental - UV resistance - All exposed materials are UV stabilized
- Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P
- Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous
- Mechanical - Cord Accommodation - 0.375"-0.875" (9.5-22.2)

General

Catalog Number	HBL26W76
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Item Type	20A Watertight Twist-Lock® Plug
Number Of Poles	3-Pole
Type	Plugs
UPC	783585131641

Dimensions

Dimensions	2.51 in x 2.51 in x 3.96 in
Height	3.96 in
Length	2.51 in

Width 2.51 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	Min. Cord: 16/3 SJ, 18/3 S, 18/4 SJ, 18/4 S, 18/5 S;Max. Cord: 10/3 S, 10/4 S, 10/5 S

Certifications And Compliance

Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	L16-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	960

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBL26W76](#)
- [Warranty - Industrial & Commercial Products](#)