HUBBELL Wiring Device-Kellems

Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems Catalog # HBL2711

Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30P, Screw Terminal, Black and White.

Performance

- Electrical Current Interrupting Certified for current interrupting at full rated current
- Electrical Dielectric Voltage Withstands 2,000V minimum
- Environmental Flammability HB or better per UL94/CSA 22.2 No.0.17
- Environmental Moisture Resistance IP20 Suitability
- Environmental Operating Temperatures Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical Terminal Accommodation #16 AWG #8 AWG stranded copper wire only.
- · Mechanical Terminal Identification Terminals identified in accordance with UL 498

General

Catalog Number HBL2711 Color Noir, blanc Cord Range 0.350"-1.150" (9-29) **EU RoHS Indicator Environmental Conditions** Indoor Dry Unless Protected By Additional Means Horsepower - Maximum 2(2)30A Grounding Insulgrip® Plug Item Type Material Nylon Material - Mounting Hardware Cord Mounted Number Of Poles 3-Pole Operating Temperature Maximum continuous 75°C and minimum -40°C without Impact

· Assembly Screws - Steel -

• Housing / Cord Clamp -

steel - nickel plated

polycarbonate

• Terminal Retainer - Clear

• Terminal Clamp - Cold rolled

nickel plated · Blades - Brass

Specifications



• Terminal Screws - #10-32 Brass (Phillips / Slotted /

Robertson)

Plugs

UPC 783585039145

Dimensions

Туре

Dimensions 2.33 in x 2.33 in x 2.75 in Standard Sized Display Size 2.75 in Height Length 2.33 in Weight 0.25 lb Width 2.33 in

Electrical Ratings

Amperage Rating 30 A Connectivity Pressure Terminal Screws Current / Amperage Rating 30 A Current Rating 30 A Dielectric Strength Withstands 2,000V minimum Single Phase Phase Voltage Rating 125/250 VAC Voltage Rating Description 125/250 VAC

Conductor Related

Cable Range 0.350 - 1.150 in Cord Type All Listed Portables Number Of Wires 4-Wire

Wire Size #16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)

• Certified to CSA C22.2

No.42

• Fed.Spec. W-C-596

• Listed to UL 498 L14-30P

Nema Rating

Standards - RoHS Compliance CM

Status

Logistics

Carton Quantity 30 Pallet Quantity 3060

Product Assets

Catalogs - WDK Catalog Full 2024 Specifications - HBL2711 Warranty - Industrial & Commercial Products



©2024 Hubbell Incorporated. All rights reserved WDK_MX-HBL2711-SPEC-EN | REV 10/2024