

# Locking Devices, Twist-Lock®, Safety Shroud, 2-Gang Surface Mount Receptacle, 30A 3-Phase Delta 250V AC, L15-30R

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2720SR2](#)



Locking Devices, Twist-Lock®, Safety-Shroud®, 2-Gang Surface Mount Receptacle, 30A 3-Phase Delta 250V AC, 3- Pole 4-Wire Grounding, NEMA L15-30R, Screw Terminal, Gray.

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL2720SR2
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	30A Safety-Shroud® Receptacle
Material	Valox™
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Number of Gang(s)	2-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Body Contact Carrier - Natural (white) nylon</li><li>• Body Holding Screws - Steel, zinc plated</li><li>• Contacts - Brass</li><li>• Housing / Flange - Gray RPT</li><li>• Terminal Retainer - Clear polycarbonate</li></ul>
Type	Receptacle
UPC	783585234762

## Dimensions

Dimensions	5.12 in x 5.12 in x 2.22 in
Display Size	Standard Sized Product
Height	2.22 in
Length	5.12 in
Weight	0.65 lb
Width	5.12 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Fed.Spec. W-C-596</li><li>• Listed to UL 498</li></ul>
Nema Rating	L15-30R

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL2720SR2](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL2720SR2-SPEC-EN | REV 10/2024