

## Locking Devices, Twist-Lock®, Safety Shroud, Male Plug, 30A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, L15- 30P, Screw Terminal, Black and White



By Hubbell Wiring Device-Kellems  
Catalog # [HBL2721S](#)

Twist-Lock® Safety-Shroud® Male Plug, 30A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, NEMA L15- 30P, Screw Terminal Nylon Body PBT Shroud

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Accommodation - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL2721S
Cord Range	0.350"-1.150" (9-29)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	30A Safety-Shroud® Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Steel - nickel plated</li><li>• Blades - Brass</li><li>• Housing / Cord Clamp - Nylon</li><li>• Safety-Shroud® - White PBT</li><li>• Terminal Clamp - Cold rolled steel - nickel plated</li><li>• Terminal Retainer - Clear polycarbonate</li></ul>

Type  
UPC

- Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- Plugs  
783585234786

### Dimensions

Dimensions	2.33 in x 2.33 in x 4.21 in
Display Size	Standard Sized
Height	4.21 in
Length	2.33 in
Weight	0.45 lb
Width	2.33 in

### Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

### Conductor Related

Cable Range	0.350 - 1.150 in
Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Fed.Spec. W-C-596</li><li>• Listed to UL 498</li></ul>
Nema Rating	L15-30P

## Logistics

Carton Quantity	10
Pallet Quantity	2160

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL2721S](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL2721S-SPEC-EN | REV 10/2024