

HUBBELL
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,
Watertight Safety Shroud,
Receptacle, 30A 3-Phase Delta
480V AC, 3-Pole 4-Wire Grounding,
L16-30R, Screw Terminal, Gray**

By Hubbell Wiring Device-Kellems
Catalog # [HBL2730SW](#)

Locking Devices, Twist-Lock®, Watertight Safety-Shroud®,
Receptacle, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire
Grounding, NEMA L16-30R, Screw Terminal, PBT housing and
flange, Gray



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2730SW
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Horsepower - Maximum	10
Item Type	30A Watertight Safety-Shroud® Receptacle
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature Specifications	-40°C to 85 °C <ul style="list-style-type: none">• Body Contact Carrier - Natural (white) nylon• Contacts - Brass• Drive Screws - Steel, zinc plated• Housing / Cover - Gray RPT• Lift-Cover Spring & Pin - Stainless Steel• Terminal Retainer - Clear polycarbonate
Type	Receptacle
UPC	783585231907

Dimensions

Dimensions	3.75 in x 3.75 in x 2.9 in
Display Size	Standard Sized Product
Height	2.9 in
Length	3.75 in
Weight	0.65 lb
Width	3.75 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	480 V
Voltage Rating Description	3 Phase 480 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L16-30R

Logistics

Carton Quantity	5
Pallet Quantity	1000

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL2730SW](#)
[Warranty - Industrial & Commercial Products](#)

