

Locking Devices, Twist-Lock®, Safety Shroud, Male Plug, 30A 3-Phase 600V AC, 3-Pole 4-Wire Grounding, L17- 30P, Screw Terminal, Black and White



By Hubbell Wiring Device-Kellems
Catalog # [HBL2741S](#)

Locking Devices, Twist-Lock®, Safety-Shroud®, Male Plug, 30A 3-Phase 600V AC, 3-Pole 4-Wire Grounding, NEMA L17- 30P, Screw Terminal, Black and White Nylon Body, White PBT Shroud.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Accommodation - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2741S
Cord Range	0.350"-1.150" (9-29)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Safety-Shroud® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Steel - nickel plated• Blades - Brass• Housing / Cord Clamp - Nylon• Safety-Shroud® - White PBT• Terminal Clamp - Cold rolled steel - nickel plated• Terminal Retainer - Clear polycarbonate

Type
UPC

- Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- Plugs
783585234946

Dimensions

Dimensions	2.33 in x 2.33 in x 4.21 in
Display Size	Standard Sized
Height	4.21 in
Length	2.33 in
Weight	0.45 lb
Width	2.33 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	600 V
Voltage Rating Description	600 V

Conductor Related

Cable Range	0.350 - 1.150 in
Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L17-30P

Logistics

Carton Quantity 10

Catalogs - WDK Catalog Full 2024
Specifications - HBL2741S
Warranty - Industrial & Commercial Products

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2741S-SPEC-EN | REV 10/2024