

HUBBELL
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,
Safety-Shroud® Receptacle, 30A, 3
Phase Y 120/208V AC, 4 Pole, 5
Wire Grounding, NEMA L21-30R**

By Hubbell Wiring Device-Kellems
Catalog # [HBL2810SR](#)

Locking Devices, Twist-Lock®, Safety-Shroud® Receptacle, 30A,
3 Phase Y 120/208V AC, 4 Pole, 5 Wire Grounding, NEMA L21-
30R, RPT surface mounting, one gang, Gray



Performance

- Electrical-Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)

General

Catalog Number	HBL2810SR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	30A Safety-Shroud® Receptacle
Listings	<ul style="list-style-type: none">• UL 498• Fed.Spec. W-C-596• CSA C22.2 No.42
Material	Valox™
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Body Contact Carrier - Natural (white) nylon• Body Holding Screws - Steel, zinc plated• Contacts - Brass• Housing / Flange - Gray RPT• Terminal Retainer - Clear polycarbonate

UPC

783585235066

Dimensions

Dimensions	4.56 in x 2.84 in x 1.71 in
Display Size	Standard Sized Product
Height	1.71 in
Length	4.56 in
Weight	0.5 lb
Width	2.84 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	3 Phase WYE
Voltage Rating	120/208 VAC

Conductor Related

Number Of Wires	5-Wire Grounding
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L21-30R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL2810SR](#)
[Warranty - Industrial & Commercial Products](#)

