

Locking Devices, Twist-Lock®, Watertight Safety Shroud, Male Plug, 30A 3-Phase 120/208V AC, 4- Pole 5-Wire Grounding, L21-30P, Screw Terminal and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL2811SW](#)

Locking Devices, Twist-Lock®, Watertight Safety-Shroud®, Male Plug, 30A 3-Phase WYE 120/208V AC, 4-Pole 5-Wire Grounding, NEMA L21-30P, Screw Terminal, Black PBT housing, White PBT clamps.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V0 per UL94 or CSA 22.2 No.0.17
- Environmental - Moisture Resistance - Type 4, 4X, 12, IP66 suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2811SW
Cord Range	0.350"-1.150" (9-29)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Watertight
Horsepower - Maximum	3
Item Type	30A Watertight Safety-Shroud® Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 60°C and minimum -29 °C
Specifications	<ul style="list-style-type: none">• Assembly Screws - Stainless Steel• Blades - Brass• Closure Plug - Santoprene• Housing / Cord Clamp - PBT• Terminal Clamp - Cold rolled steel - nickel plated• Terminal Retainer - Clear polycarbonate



Type
UPC

- Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
 - Watertight Gland - Neoprene
- Plugs
783585232089

Dimensions

Dimensions	2.94 in x 2.94 in x 4.40 in
Display Size	Standard Sized
Height	4.4 in
Length	2.94 in
Weight	0.7 lb
Width	2.94 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	3 Phase WYE
Voltage Rating	3 Phase WYE 120/208 VAC
Voltage Rating Description	3-Phase Y 120/208 VAC

Conductor Related

Cable Range	0.350 - 1.150 in
Cord Type	All Listed Portables
Number Of Wires	5-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L21-30P

Logistics

Carton Quantity 10

Catalogs - WDK Catalog Full 2024
Specifications - HBL2811SW
Warranty - Industrial & Commercial Products

Product Assets

