

Watertight Devices, Twist-Lock® Plug, 30A, 125/250V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L14-30P, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL28W74](#)



Watertight Devices, Twist-Lock® Plug, 30A, 125/250V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L14-30P, Yellow

General

Catalog Number	HBL28W74
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Item Type	30A Watertight Twist-Lock® Plug
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none">Electrical - Current Interrupting - Rated for current interruption per UL498Electrical - Dielectric Voltage - 2500V ACElectrical - Max Working Voltage - As markedElectrical - Temperature Rise - 30°C max per UL498 at rated currentEnvironmental - UV resistance - All exposed materials are UV stabilizedEnvironmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6PEnvironmental - Operating Temperatures - -40°C (without impact) to +60°C continuousMechanical - Cord Accommodation - 0.375"-1.000" (9.5-25.4)
Type	<ul style="list-style-type: none">PlugsPlugs
UPC	783585131702

Dimensions

Dimensions	2.77 in x 2.77 in x 3.94 in
Height	3.94 in
Length	2.77 in
Width	2.77 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	Min Cords: 12/3 SJ, 16/3 S, 14/4 SJ, 18/4 S, 18/5 S;Max Cord: 8/3 S, 8/4 S, 10/5 S

Certifications And Compliance

Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	L14-30P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	660

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)

