



## Wallplates and Boxes, Marine Products, 24-32V DC, Male Plug, For Trolling Motor, Yellow, Corrosion Resistant

By Hubbell Wiring Device-Kellems  
Catalog # [HBL328DCP](#)



Marine 24-32V DC Male Plug, for Trolling Motor, Corrosion Resistant

### Application

Electric Fishing Reel Devices

### General

Color	Yellow
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Insulgrip
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
UPC	783585353128

### Dimensions

Display Size	Standard Sized
--------------	----------------

### Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	28V DC kV
Voltage Rating Description	28V DC kV
Wattage	840

### Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #8 AWG

### Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Wiring\\_Catalog\\_BB34\\_CatPage](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL328DCP-SPEC-EN | REV 1/2024