



Wiring Device-Kellems

# PS, IEC, PLUG, 2P3W, 30A 550VDC, MAT MOD

By Hubbell Wiring Device-Kellems  
Catalog # [HBL330P8V0DC](#)



PS, IEC, PLUG, 2P3W, 30A 550VDC, MAT MOD

## General

Color	Black
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstand 3000V AC</li> <li>• Electrical - Max. Working Voltage - 600V RMS</li> <li>• Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17</li> <li>• Environmental - Ingress Protection - IP67 Suitability</li> <li>• Environmental - Moisture Resistance - Watertight per IEC 60309-1</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C</li> <li>• Minimum - 40°C w/o impact</li> <li>• Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device housing</li> <li>• Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions</li> </ul>

Series	DC Rated
Style	Standard Service
Type	Watertight Plug
UPC	783585242279

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified File LR280C</li> <li>• UL Classified to IEC 60309-1 IEC 60309-2</li> <li>• UL Listed, File E146033</li> </ul>
----------------------	--

## Product Assets

[Catalog Page - Wiring G-13 Catalog page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

Voltage Rating 550 VDC  
Voltage Rating Description 550 VDC

---



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL330P8V0DC-SPEC-EN | REV 1/2024