



Wiring Device-Kellems

Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 125/250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, White

By Hubbell Wiring Device-Kellems
 Catalog # [HBL3334C](#)



Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 125/250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

Application

Extra Heavy Duty Industrial

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Non-Grounding Insulgrip® Flanged Inlet
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture Resistance - IP20 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact) • Mechanical - Terminal Accommodation - #16

Dimensions

Dimensions	2.88 in x 2.88 in x 2.22 in
Display Size	Standard Sized Product
Height	2.22 in
Length	2.88 in
Weight	0.2 lb
Width	2.88 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
----------------------	---

Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Recommendation #10
AWG - #8 AWG solid or
stranded copper wire only.

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with UL 498

Type
UPC

Flanged Inlet
783585039855



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL3334C-SPEC-EN | REV 1/2024