



Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 3-Phase 120/208VAC, 4-Pole 4-Wire Non-Grounding, Non- NEMA, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL3431C](#)



Twist-Lock® Industrial Male Plug, 30A 3-Phase 120/208VAC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw Terminal

Features

- Ribbed nylon housing provides a secure grip and impact and chemical resistance
- Superior cord grip design protects terminations from excess strain
- Clear, funnel shaped wire entry for ease of termination
- Integral dust shield protects wiring chamber from dust or contaminants

Application

Extra Heavy Duty Industrial

General

Color	Black, White
Cord Range	0.350"-1.150" (9-29)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Non-Grounding Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal

Dimensions

Dimensions	2.33 in x 2.33 in x 2.75 in
Display Size	Standard Sized
Height	2.75 in
Length	2.33 in
Weight	0.3 lb
Width	2.33 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3 Phase WYE 120/208 VAC
Voltage Rating Description	3 Phase WYE 120/208 VAC

Conductor Related

Cable Range	0.350 - 1.150 in
Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
----------------------	---

Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Mechanical - Terminal
Accommodation - #16
AWG - #8 AWG stranded
copper wire only.

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with UL 498

Type

- Plugs
- Plugs

UPC

783585039879



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL3431C-SPEC-EN | REV 1/2024