

HUBBELL
Wiring Device-Kellems

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 60A 250V AC, 2-Pole 3-Wire Grounding, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL360C6W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 60A 250V AC, 2-Pole 3-Wire Grounding, Terminal Screws, Blue, Watertight



General

Application	High Ampacity Connections
Catalog Number	HBL360C6W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current
	Electrical - Dielectric Voltage - Withstand 3000V AC
	Electrical - Max. Working Voltage - 600V RMS
	Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
	Environmental - Ingress Protection - IP67 Suitability
	Environmental - Moisture Resistance - Watertight per IEC 60309-1
	Environmental - Operating Temperatures - Maximum Continuous 75°C
	Minimum - 40°C w/o impact
	Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
	Mechanical - Product Identification - Ratings are a permanent part of the device housing
	Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions
Series	HBL Heavy Duty
Style	Standard Service
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Watertight Connector Body
UPC	783585403786

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

Conductor Related

Conductor Range	#8 AWG to #2 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Industry Standard(s)	CSA Certified File LR280C UL Classified to IEC 60309-1 IEC 60309-2 UL Listed, File E146033
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
Pallet Quantity	180

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL360C6W-SPEC-EN | REV 6/2024