

Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 20A 347V AC, 2-Pole 3-Wire Grounding, L24-20R, Screw Terminal, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL3720](#)



Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 20A 347V AC, 2-Pole 3-Wire Grounding, NEMA L24-20R, Screw Terminal, Nylon face, Back and side wire, Black.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL3720
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single Flush Receptacles
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Base - Glass-Reinforced thermoplastic polyester (RTP)• Contacts - Brass• Face - Nylon• Mounting Strap - Brass• Terminal Screws - #10 - 32 Brass
Type	Single Flush Receptacle
UPC	783585046587

Dimensions

Dimensions	3.28 in x 1.23 in x 1.7 in
Display Size	Standard Sized Product
Height	1.7 in
Length	3.28 in
Weight	0.25 lb
Width	1.23 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	347 VAC
Voltage Rating Description	347 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	L24-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL3720](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_MX-HBL3720-SPEC-EN | REV 1/2025