

Locking Devices, Twist-Lock®, Industrial, Receptacle, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Phenolic, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL3769](#)



Locking Devices, Twist-Lock®, Industrial, Receptacle, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Phenolic, Black

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #10 AWG - #6 AWG solid or stranded copper wire only

General

Catalog Number	HBL3769
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Receptacle
Material	Phenolic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Body - Phenolic• Contacts - Brass• Face - Phenolic• Insulator - Phenolic• Terminal Screws - Steel
Type	Receptacle
UPC	783585236469

Dimensions

Dimensions	3.28 in x 2.12 in x 2.36 in
Display Size	Standard Sized Product

Height	2.36 in
Length	3.28 in
Weight	0.75 lb
Width	2.12 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Multi Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Listed to UL 498
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	1000

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL3769](#)
[Warranty - Industrial & Commercial Products](#)