

## Straight Blade Devices, Receptacles, 4- Plex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 15A 125V, 5- 15R, Brown, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL415](#)

Straight Blade Devices, Receptacles, 4- Plex,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A  
125V, 5- 15R, Brown, Single Pack.

### Application

- Industrial

### Performance

- Electrical - Current Interrupting - Capable of withstanding a fault level of 1000A, per UL498
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-12 AWG stranded or solid copper conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### General

Catalog Number	HBL415
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	4-PLEX
Material	Polycarbonate
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	4-Outlet Receptacle
Specifications	<ul style="list-style-type: none"><li>Base - PBT</li><li>Face - Polycarbonate</li><li>Ground Contacts - .031 in. (.8) Brass</li><li>Ground Plate - .032 in. (.8) Plated Steel</li></ul>



UPC

- Power Contacts - .032 in. (.8) Brass
- 783585014081

### Dimensions

Dimensions	4.30 in x 0.92 in x 4.30 in
Display Size	Standard Sized Product
Height	4.3 in
Length	4.3 in
Weight	0.4 lb
Width	0.92 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>Certified to CSA 22.2, No. 42 File 285</li><li>Listed to UL Standard 498 File E2186</li><li>NEMA® WD-6 Compliant 5-15R</li></ul>
Nema Rating	5-15R

### Logistics

Carton Quantity	5
-----------------	---



A Hubbell brand