

## Straight Blade Devices, Receptacles, 4- Plex, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Ivory, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL415HI](#)



Straight Blade Devices, Receptacles, 4- Plex, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Ivory, Single Pack.

### Application

- 4-Plex Hospital Grade

### Performance

- Electrical - Current Interrupting - Capable of withstanding a fault level of 1000A, per UL498
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#12 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### General

Catalog Number	HBL415HI
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	4-PLEX
Material	Polycarbonate
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	4-PLEX Receptacle
Specifications	<ul style="list-style-type: none"> <li>• Base - PBT</li> <li>• Face - Polycarbonate</li> <li>• Ground Contacts - .031 in. (.8) Brass</li> <li>• Ground Plate - .032 in. (.8) Plated Steel</li> <li>• Power Contacts - .032 in. (.8) Brass</li> </ul>
Style	Smooth Face

Type	4-PLEX Receptacle
UPC	783585015767

### Dimensions

Dimensions	4.3 in x 4.3 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	4.3 in
Weight	0.4 lb
Width	4.3 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA, C22.2, No. 42 File 285</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2186</li> </ul>
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	5
Pallet Quantity	1440



A Hubbell brand