



# 4-PLEX Surge Suppression Receptacle, 2- Pole 3-Wire, 15A 125V, 5-15R, Blue

By Hubbell Wiring Device-Kellems  
Catalog # [HBL415S](#)



4-PLEX Surge Suppression Receptacle, 2- Pole 3-Wire, 15A 125V, 5-15R, Blue.

## Features

- Surge suppression with lights, 80 joules/6500A per mode
- Anchor hole and loop feature secures solid wire for fast, easy terminations
- Triple wipe contacts
- Easily accessible break-off tabs for split wiring
- Three conductors energize all four outlets

## Application

4-Plex with LED

## General

Color	<ul style="list-style-type: none"> <li>• Blue</li> <li>• Bleu</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.50
Indicator(s) Type	LED Only
Item Type	Surge Protection Receptacles
Material	Polycarbonate
Material - Mounting Hardware	Mounting Screws
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Capable of withstanding a fault level of 1000A, per UL498</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - UL 94 V-2</li> <li>• Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li> <li>• Mechanical - Terminal Accommodation - #14-12</li> </ul>

## Dimensions

Dimensions	4.30 in x 0.92 in x 4.30 in
Display Size	Standard
Height	4.30 in
Length	4.30 in
Weight	0.35 lb
Width	0.92 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA 22.2, No. 42 File 285</li> <li>• Listed to UL Standard 498 File E2186</li> <li>• NEMA® WD-6 Compliant</li> </ul>
----------------------	--

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

Accommodation - #14-12  
AWG stranded or solid  
copper conductor only

- Mechanical - Terminal  
Identification - Terminals  
identified in accordance  
with UL 498 and CSA

Response Time  
Series  
UPC

5  
4-Outlet Receptacle  
783585017853



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL415S-SPEC-EN | REV 1/2024