

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Mechanically Interlocked Receptacle, 30A 3-Phase Delta 600V AC,

By Hubbell Wiring Device-Kellems
Catalog # [HBL430MI5W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Mechanically Interlocked Receptacle, 30A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, Terminal Screws

Application

- High Ampacity Watertight Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage
- Electrical - Dielectric Voltage - Withstands 3,000V AC Min
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V-0 Classification
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Outdoor - 4X (Watertight, Washdown)
- Indoor - 12 (Dust-tight, Falling Dirt and Noncorrosive Liquids).
- Environmental - Operating Temperature - Max. Continuous +75°C
- Min. Continuous -40°C
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - External adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of the external label and molded into the receptacle mount
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

General

Catalog Number	HBL430MI5W
Color	Noir
EU RoHS Indicator	No
Environmental Conditions	Watertight
Item Type	Mechanically Interlocked Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Non-Fused
Specifications	<ul style="list-style-type: none">• Base - Valox®• Conduit Hub - Zinc



Style
Type
UPC

Dimensions

Display Size

Electrical Ratings

Amperage Rating
Connectivity
Current / Amperage Rating
Current Rating
Phase
Voltage Rating
Voltage Rating Description
Wattage

Conductor Related

Number Of Wires
Wire Size

Certifications And Compliance

Industry Standard(s)
Nema Rating

Logistics

Carton Quantity

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL430MI5W](#)

- Enclosure Gasket - Neoprene
 - Face - Valox®
 - Shaft Seal - Neoprene
- Standard Service
Mechanical Interlock
783585405964

Standard Sized Product

30 A
Pressure Terminal Screws
30 A
30 A
Three Phase
3 Phase 600 VAC
3 Phase 600 VAC
18000

4-Wire
#12 AWG to #8 AWG

UL Listed
Non-NEMA

1



A Hubbell brand