



Wiring Device-Kellems

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Mechanically Interlocked Receptacle, 30A 3-Phase Delta 250V AC,

By Hubbell Wiring Device-Kellems
Catalog # [HBL430MI9WR](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Mechanically Interlocked Receptacle, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Terminal Screws

Features

- Captured neoprene gasket for a watertight seal
- DIN rail mounted switch for easy installation and replacement
- Solid pins for longer life and reliable electrical contact

Application

High Ampacity Watertight Connections

General

Color	<ul style="list-style-type: none"> • Blue • Bleu
Environmental Conditions	Watertight
Item Type	Mechanically Interlocked Single, Reversed
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage • Electrical - Dielectric Voltage - Withstands 3,000V AC Min • Electrical - Max. Working Voltage - 600V AC RMS • Environmental - Flammability - UL94-5VA and V-0 Classification • Environmental - Ingress Protection - IP67 Suitability • Environmental - Moisture Resistance - Outdoor - 4X (Watertight, Washdown) • Indoor - 12 (Dust-tight, Falling Dirt and Noncorrosive Liquids). • Environmental - Operating Temperature - Max.



Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase 240 VAC
Voltage Rating Description	3 Phase 240 VAC
Wattage	7500

Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	Non-NEMA

Product Assets

[Catalog Page - Wiring G-21 Catalog page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

- Temperature - Continuous +75°C
- Min. Continuous -40°C
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - External adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of the external label and molded into the receptacle mount
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Series
Style
Type

UPC

Non-Fused
Reverse Service

- Mechanical Interlock
- Mechanical Interlock

783585012605



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL430M19WR-SPEC-EN | REV 1/2024