



Wiring Device-Kellems

HBL45123R20

By Hubbell Wiring Device-Kellems
Catalog # [HBL45123R20](#)

Cord and Cable Reels, Industrial Cord Reel, With Box and 5352GRY, 45' 12/3, Yellow



Features

- Multi-position guide arm
- Positive-latch mechanism maintains desired cord length
- 12 AWG cord for greater current carrying capacity
- Plug-in 5 ft. long power cord requires no electrical wiring

Application

Bench, Ceiling and Wall Mounted

General

Base Type	Optional
Cable Length	45 Ft
Cable Type	#12/6 SJ
Construction	Steel
Duty	Heavy Duty
EU RoHS Indicator	Yes
Item Type	Reel with Portable Outlet Box and 1 Duplex Plate
Performance	Environment - Operations - Dry, indoor, non-hazardous locations
Series	Industrial
Type	Real With Portable Outlet Box An 1-20A 125V Duplex Receptacle
UPC	783585451282

Dimensions

Cable Length Active	540
Cable Length Inactive	60
Reel Frame Dimension	Steel

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Conductor Related

Cable Specification	12/3 SJEO
Feeder Cord	12/3 SJEO
Nema Color	Yellow and Black

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA C22.2 No. 21 Certified • UL 355 Listed
----------------------	---

Product Assets

[Catalogs - WDK Catalog Full 2023](#)



A proud member of the Hubbell Family.