

Twist-Lock®, Industrial, Combo Face Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R and L5-15R, Screw Terminal, Brown, 1) Feed 1) Return

By Hubbell Wiring Device-Kellems
Catalog # [HBL4792](#)



Twist-Lock® Industrial Combination Face Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R and L5-15R, Screw Terminal, One Feed One Return

Features

- Industrial
- Combo Face Duplex Receptacle
- 15A 125V
- 2-Pole 3-Wire Grounding

Application

Heavy Duty

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2 or better
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL4792
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Combination Duplex Receptacles
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Series

Special Combination Receptacle

Specifications

- Base - Reinforced thermoplastic polyester
- Face - Reinforced thermoplastic polyester
- Power Contacts - .032" (.81) Brass

Style

Finder Groove Face

Type

Duplex Receptacle

UPC

783585236995

Dimensions

Dimensions	3.28 in x 1.5 in x 0.88 in
Display Size	Standard Sized Product
Height	0.88 in
Length	3.28 in
Weight	0.3 lb
Width	1.5 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285
----------------------	--

Nema Rating
Standards - RoHS Compliance
Status

- UL Listed to UL498 File E2186

5-15R, L5-15R
CM

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL4792](#)
[Warranty - Industrial & Commercial Products](#)

Logistics



A Hubbell brand