

Locking Devices, Twist-Lock®, Marine Grade, Shore Power Inlet, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, White

By Hubbell Wiring Device-Kellems
Catalog # [HBL504NM](#)



Locking Devices, Twist-Lock®, Marine Grade, Shore Power Inlet, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, White

Application

Marine Wiring Devices

Performance

Environmental - Moisture Resistance - IP55 Suitability

General

Catalog Number	HBL504NM
Color	<ul style="list-style-type: none">White
EU RoHS Indicator	No
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Hull Mount Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
UPC	783585519470

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 3000V Minimum in
Phase	Single Phase
Voltage Rating	125/250 VAC
Wattage	12500

Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	#6 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	5
Pallet Quantity	455

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)