



Straight Blade Devices, Receptacles, Single, Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5251](#)



Straight Blade Devices, Receptacles, Single, Industrial Grade,
2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown, Single Pack.

Features

- Slender/compact design
- Triple wipe contacts

Application

Heavy Duty

General

Color	<ul style="list-style-type: none"> • Brown • Marron
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-0 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only • Mechanical - Terminal Identification - Terminals identified in accordance

Dimensions

Dimensions	3.28 in x 1.39 in x 1.13 in
Display Size	Standard Sized Product
Height	1.13 in
Length	3.28 in
Weight	0.15 lb
Width	1.39 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired Only
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 • Fed. Spec. WC596 • NEMA® WD-6 Compliant • UL Listed, File E2186
----------------------	--

Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Identified in accordance
with UL 498 and CSA

Series	Heavy Duty
Style	Finder Groove Face
Type	<ul style="list-style-type: none">• Single Receptacle• Single Receptacle
UPC	783585013817



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL5251-SPEC-EN | REV 1/2024