




Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5262](#)



Straight Blade Devices, Receptacles, Duplex, Industrial Grade,
2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown, Single Pack.

Features

- Back wired ground terminal allows faster, easier installation
- One-piece brass integral ground strap
- Finder Groove Face
- Deep body design with circuit ID face

Application

Extra Heavy Duty Specification Grade

General

Color	<ul style="list-style-type: none"> • Brun • Marron
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10

Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

AWG copper stranded or solid conductor only

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series

Extra Heavy Duty

Style

Finder Groove Face

Type

- Standard Duplex
- Standard Duplex

UPC

783585435107



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL5262-SPEC-EN | REV 1/2024