

**HUBBELL**  
Wiring Device-Kellems

**Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 30A 3-Phase Wye 120/208V AC, Watertight**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL530C9W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 30A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Terminal Screws, Blue, Watertight



## General

Application	High Ampacity Connections
Catalog Number	HBL530C9W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current
	Electrical - Dielectric Voltage - 3000V AC
	Electrical - Max. Working Voltage - 600V RMS
	Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
	Environmental - Ingress Protection - IP67 Suitability
	Environmental - Moisture Resistance - Watertight per IEC 60309-1
	Environmental - Operating Temperatures - Maximum Continuous 75°C
	Minimum - 40°C w/o impact
	Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682
	Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing
	Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions
Series	HBL Heavy Duty
Style	Standard Service
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Watertight Connector Body
UPC	783585405452

## Dimensions

Display Size	Standard
--------------	----------

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC

## Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	5-Wire
Number of Conductors	5-Wire Grounding

## Certifications And Compliance

Industry Standard(s)	CSA Certified File LR280C UL Classified to IEC 60309-1 IEC 60309-2 UL Listed, File E146033
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	10
Pallet Quantity	280

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL530C9W-SPEC-EN | REV 6/2024