



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL53421](#)



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.

Features

- Slender/compact design
- Brass Mounting Strap
- Triple wipe contacts

Application

Extra Heavy Duty Compact

General

Color	Ivory
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only • Mechanical - Terminal Identification - Terminals identified in accordance
-------------	--

Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Standard Sized Product
Height	1.05 in
Length	3.28 in
Weight	0.25 lb
Width	1.33 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired Only
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Fed. Spec. WC596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

with UL 498 and CSA

Series	Heavy Duty
Style	Finder Groove Face
Type	Standard Duplex
UPC	783585434803



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL5342I-SPEC-EN | REV 1/2024