

Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, White, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5352W](#)



Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, White, Single Pack.

Application

- Extra Heavy Duty Compact

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5352W
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Heavy Duty
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Clip - Stainless steel• Base - RTP• Contacts - Brass• Face - Nylon• Mounting Screws - Steel-Zinc Plated• Mounting Strap - .031" (.8) Brass

Style
Type
UPC

- Terminal Screws - Brass
 - Wire Clamp - Plated brass
- Finder Groove Face
Standard Duplex
783585435084

Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Standard Sized Product
Height	1.05 in
Length	3.28 in
Weight	0.2 lb
Width	1.33 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Certified Listed	Buy American Act Compliant, BABA Compliant (All status valid till December 2024)
Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA 22.2, No. 42 File 285• Fed. Spec. W-C596G• NEMA® WD-6 Compliant

- UL Listed to UL498 File No. E2186

Carton Quantity 10
Pallet Quantity 3600

Nema Rating 5-20R
Standards - RoHS Compliance CM
Status

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL5352W](#)
[Warranty - Industrial & Commercial Products](#)

Logistics



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5352W-SPEC-EN | REV 10/2024