


**HUBBELL**  
Wiring Device-Kellems

**Straight Blade Devices,  
Receptacles, Duplex, Industrial  
Grade, 2-Pole 3-Wire Grounding,  
20A 125V, 5-20R, Gray, Single Pack**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5362GY](#)

Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-  
Pole 3-Wire Grounding, 20A 125V, 5-20R, Gray, Single Pack



## General

Application	Extra Heavy Duty Specification Grade
Catalog Number	HBL5362GY
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current  Electrical - Dielectric Voltage - Withstands 2,000V minimum  Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0  Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)  Mechanical - Product Identification - Ratings are a permanent part of the device  Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only  Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Standard Duplex  Standard Duplex
UPC	783585435268

## Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA 22.2, No. 42 File 285  Fed. Spec. W-C-596  NEMA® WD-6 Compliant  UL Listed to UL498 File No. E2186
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL5362GY-SPEC-EN | REV 6/2024