

Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5366CA](#)



Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P, Black and White, Single Pack.

Application

- Industrial/Commercial Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5366CA
Color	Black, White
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.15
Item Type	Insulgrip Plug
Material	Polycarbonate
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Insulgrip®
Specifications	<ul style="list-style-type: none">• Assembly Screws - Nickel plated steel• Blade Holder - Nylon• Blades - .060 in. (1.5) Brass• Housing/Cord Clamp - Nylon• Terminal Clamp - Nickel plated steel• Terminal Retainer - Clear Polycarbonate

Style
Type
UPC

- Terminal Screws - #8-32 Brass , multiple drive
- Angled
Plug
783585174006

Dimensions

Dimensions	1.21 in x 1.52 in x 2.08 in
Height	2.08 in
Length	1.21 in
Weight	0.15 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified to C22.2 No. 42 File 280• Fed. Spec. W-C596G• NEMA® WD-6 Compliant• UL Listed to UL498 File E1706
Nema Rating	5-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity 10
Pallet Quantity 4500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL5366CA](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5366CA-SPEC-EN | REV 10/2024