



Straight Blade Devices, Male Plug, Corrosion Resistant, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 20A 125V, 5-20P, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL53CM66C](#)



Straight Blade Male Plug, Corrosion Resistant, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P

Features

- Ribbed nylon housing is impact and chemical resistant
- VARI-SIZE adjustable cord clamp
- Fast lead assembly screws
- Beveled housing prevents snagging

Application

Industrial/Commercial Grade

General

Color	<ul style="list-style-type: none"> • Yellow • Jaune
Horsepower - Maximum	2
Item Type	Insulgrip Plug
Material	Polycarbonate
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 HB or better • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only • Mechanical - Terminal Identification - Terminals

Dimensions

Dimensions	1.52 in x 1.52 in x 1.96 in
Height	1.96 in
Length	1.52 in
Weight	0.2 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No. 42 File 280 • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706
----------------------	---

Nema Rating	5-20P
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Identification terminals
identified in accordance
with UL 498 and CSA

Series	Insulgrip
Style	Corrosion Resistant
Type	<ul style="list-style-type: none">• Plugs• Plugs
UPC	783585161709



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL53CM66C-SPEC-EN | REV 1/2024